


INSTRUCTION MANUAL



Rondoo DL Satin 44970
Rondoo DL White 44971

<p>1.</p>	<p>2.</p>	<p>3.</p>
<p>4.</p> <p>INPUT: AC220~240V</p>	<p>5.</p>	<p>6.</p> <p>Warning: When replacing a halogen lamp, wait for it to cool, for a minimum of 5 minutes</p>
<p>7.</p>	<p>Overall Sizes:</p>	

FittinQ B.V.

Smaragdweg 52, 5527 LB Hapert, The Netherlands
www.qazqa.nl

QAZQA