









H 80 / H 100 / HG 100 / HGH 100



Varianto

Montageanleitung / Notice de montage / Assembly instruction






2x 2x 4x




Ø 5mm 8x 8x 12x





H 30 / H 40 / H 50 / H 60 / KH 60-32 / HG 50 / HGH 50 / H 50-89 / H 60-89


Varianto Montageanleitung / Notice de montage / Assembly instruction



4x 12x 2x 1x 4x 3,5x15






8x 2x 2x Ø8mm




SPU 50 Variante Blocktype

Montageanleitung / Notice de montage / Assembly instruction



2x

4x





Ø5mm

4x

14x



4x




2x


1x

3,5x15

3,5x15





Ø 5mm



5x

3,5x30



US 40 B/ 50 B/ 60 B Varianto (Blocktype)

Montageanleitung / Notice de montage / Assembly instruction

